



- Loud electronic horn
- High life duration up to 5,000 hrs
- Integrated mounting bracket
- High protection rating IP 65

i TECHNICAL SPECIFICATIONS:

Dimensions (L x H x W):	83 mm x 84 mm x 91.5 mm
Housing:	PC, PC/ABS-Blend, grey
Fixing:	Wall mounting
Installation position:	Sound outlet facing downwards
Connection:	Screw terminal with wire protection max. 1.5 mm ²
Cable entry:	Cable diameter max. 9 mm
Tone frequency:	C. 110 Hz
Life duration:	> 5,000 hrs
Duty cycle:	100 %

🛒 ORDER SPECIFICATIONS:

Voltage	24 V AC/DC	115 V AC	230 V AC
Current consumption	≤ 80 mA	≤ 70 mA	≤ 70 mA
	585 000 75	585 000 67	585 000 68



⚠️ ADDITIONAL INFORMATION:

Thanks to the use of the most modern technology, the 584 and 585 horns have life duration of up to 5,000 hours (10 times longer than conventional horns).

The sound output can be adjusted up to 98 dB.



📐 TECHNICAL DIAGRAMS:

see page 308



See note on page 347

ERC	125 g	IP 65	+50°C -20°C	98 dB	24 V PLC
------------	-------	-------	----------------	-------	-------------

