



- High-quality stainless steel housing
- Award-winning design
- Transparent lenses ensure signalling effect even in direct sunlight

i TECHNICAL SPECIFICATIONS:

Life duration up to 50,000 hrs

Dimensions (Ø x Height):	2 tier: 42 x 220 mm 3 tier: 42 x 254 mm
Housing:	Stainless steel, brushed
Fixing:	Installation mounting for Ø 22.5 mm (M22 x 1.5 mm)
Connection:	Cable, 2 m long, included in assembly
Current consumption:	40 mA per tier

🛒 ORDER SPECIFICATIONS:

deSIGN		24 V DC
2 tier	red/green	694 010 55
	red/yellow	694 020 55
3 tier	red/yellow/green	694 000 55

🏠 ACCESSORIES:

Surface housing single	975 109 02
Bracket, stainless steel (Protection rating IP 33)	960 694 01

📏 TECHNICAL DIAGRAMS:

see page 311

Signal Towers · completely pre-assembled · deSIGN



See note on page 347

