

Ex LED Perm. Beacon 729 / Accessories

Ex Cable gland M20x1.5



Part No.: 975.729.01



MECHANICAL DATA

Height	48 mm
Materials	PA
Housing colour	Black
Protection category	IP66
Cable entry minimum	d = 7 mm
Cable entry maximum	d = 13 mm
Working temperature minimum	-40°C
Working temperature maximum	+75°C
Weight with packaging	63 g
Product weight	63 g

APPROVAL DATA

WEEE	No
Conforms with RED directive	No
Conforms with ATEX-directive	Yes
ATEX-guidance	2014/34/EU
Ex label for gas	Ex eb
Ex label for dust	Ex tb
Conforms with CCC	No
Conforms with UL	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.