

Ex LED Perm. Beacon 729 / Accessories

**Ex Cable gland M20x1.5, metal**

Part No.: 975.729.04

**MECHANICAL DATA**

Height	37 mm
Diameter	27 mm
Housing colour	Silver
Protection category	IP68
Cable entry minimum	d = 6 mm
Cable entry maximum	d = 13 mm
Working temperature minimum	-60°C
Working temperature maximum	+75°C
Weight with packaging	57 g
Product weight	50 g

**APPROVAL DATA**

WEEE	No
Conforms with RED directive	No
Conforms with ATEX-directive	Yes
ATEX-guidance	JA
Ex label for gas	Ex eb
Ex label for dust	Ex tb
Conforms with CCC	No
Conforms with UL	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	No
Conforms with AS-I	No
ICAO Certification	No
Conforms with DNV	No
Conforms with RoHS CN	No



For additional installation and mounting information, refer to the appropriate user guide at [www.werma.com](http://www.werma.com). This printed copy is for information only and is subject to alteration.