

**WA-GSC SERIES ENCLOSURES
NEMA 3 & 4 SCREW COVER MOISTURE PROOF**




WA060604GSC



WA060604GSCG

Industry Standards

UL50, Type 4
NEMA/EEMAC Type 3 & 4



FEATURES-SPECIFICATIONS

Applications

Designed for use as a wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem.

Construction

- Bodies fabricated from 14 or 12 gauge carbon steel or G-90 grade galvanized steel. Covers fabricated

from 14, 12, or G-90 grade galvanized steel

- Seams are continuously welded and ground smooth
- Cover contains closed cell oil resistant neoprene gasket
- Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc., from entering into the box through the screw holes

- Galvanized box welded corners protected by zinc-rich coating
- No holes or knockouts

Finish

- ANSI-61 gray polyester powder inside and out over phosphatized surfaces, or unpainted pre-galvanized steel

Accessories

- See pages J1-J19

WA-GSC SERIES SCREW COVER ENCLOSURES			
CATALOG NUMBER		BODY/DOOR STEEL GAUGE	ENCLOSURE SIZE W X H X D
PAINTED	GALVANIZED		
WA060604GSC	WA060604GSCG ◀	14/14	6.00x6.00x4.00 (152x152x102)
WA060606GSC ◀	WA060606GSCG ◀	14/14	6.00x6.00x6.00 (152x152x152)
WA060804GSC ◀	WA060804GSCG ◀	14/14	6.00x8.00x4.00 (152x203x102)
WA060806GSC ◀	WA060806GSCG ◀	14/14	6.00x8.00x6.00 (152x203x152)
WA080804GSC	WA080804GSCG ◀	14/14	8.00x8.00x4.00 (203x203x102)
WA080806GSC ◀	WA080806GSCG ◀	14/14	8.00x8.00x6.00 (203x203x152)
WA081004GSC ◀	WA081004GSCG ◀	14/14	8.00x10.00x4.00 (203x254x102)
WA101004GSC ◀	WA101004GSCG ◀	14/14	10.00x10.00x4.00 (254x254x102)
WA101006GSC ◀	WA101006GSCG ◀	14/14	10.00x10.00x6.00 (254x254x152)
WA101206GSC	WA101206GSCG ◀	14/14	10.00x12.00x6.00 (254x305x152)
WA121204GSC ◀	WA121204GSCG ◀	14/14	12.00x12.00x4.00 (305x305x102)
WA121206GSC	WA121206GSCG ◀	14/14	12.00x12.00x6.00 (305x305x152)
WA121606GSC ◀	WA121606GSCG ◀	14/14	12.00x16.00x6.00 (305x406x152)
WA121608GSC ◀	WA121608GSCG ◀	14/14	12.00x16.00x8.00 (305x406x203)
WA161606GSC ◀	WA161606GSCG ◀	14/14	16.00x16.00x6.00 (406x406x152)
WA161608GSC ◀	WA161608GSCG ◀	14/14	16.00x16.00x8.00 (406x406x203)
WA181806GSC ◀	WA181806GSCG ◀	14/14	18.00x18.00x6.00 (457x457x152)
WA202008GSC ◀	WA202008GSCG ◀	14/14	20.00x20.00x8.00 (508x508x203)
WA202408GSC ◀	WA202408GSCG ◀	14/14	20.00x24.00x8.00 (508x610x203)
WA242408GSC ◀	WA242408GSCG ◀	14/14	24.00x24.00x8.00 (610x610x203)
WA303012GSC ◀	WA303012GSCG ◀	12/12	30.00x30.00x12.00 (762x762x305)
WA363612GSC ◀	WA363612GSCG ◀	12/12	36.00x36.00x12.00 (914x914x305)

◀ NEW PRODUCT IN 2003



