

FEATURES-SPECIFICATIONS
Description

Panels for Free Standing NEMA 12 Enclosures and Free Standing NEMA 4 Enclosures.

- Full-length and half-length swing-out panels are available
- Half-length panels can be located in the upper or lower portion of the enclosures
- Mounting can be on either side of the enclosure
- Mounting hardware is furnished with each panel
- Panels are fabricated from 12 gauge steel
- Panels may be used in two-door enclosures along with other free-standing accessories
- Panels are painted with a white polyester powder
- **Optional "G"** panels have a conductive finish (no paint)

SWING OUT PANELS ONLY (FULL & HALF) NEMA 12 SINGLE DOOR				
CATALOG NUMBER		STEEL GAUGE	PANEL SIZE A X B	PANEL TYPE
WHITE	"G"			
WA60SP24F3	WA60SP24F3G	12	48.00x19.00 (1219x483)	Full
WA60SP24F4	WA60SP24F4G	12	24.88x19.00 (632x483)	Half
WA72SP24F3	WA72SP24F3G	12	60.00x19.00 (1524x483)	Full
WA72SP24F4	WA72SP24F4G	12	30.88x19.00 (784x483)	Half
WA72SP30F3	WA72SP30F3G	12	60.00x25.00 (1524x635)	Full
WA72SP30F4	WA72SP30F4G	12	30.88x25.00 (784x635)	Half
WA60SP36F3	WA60SP36F3G	12	48.00x31.00 (1219x787)	Full
WA60SP36F4	WA60SP36F4G	12	24.88x31.00 (632x787)	Half
WA72SP36F3	WA72SP36F3G	12	60.00x31.00 (1524x787)	Full
WA72SP36F4	WA72SP36F4G	12	30.88x31.00 (784x787)	Half
WA90SP36F3	WA90SP36F3G	12	78.00x31.00 (1981x787)	Full
WA90SP36F4	WA90SP36F4G	12	39.88x31.00 (1013x787)	Half

NOTE: If used in a Two Door Enclosure, a center panel support must be ordered.

NOTE: Suffix F3 = Full Panel, and F4 = Half Panel.

