






FRONT VIEW
WITHOUT COVER



SECTION B-B



SECTION A-A

NOTES									
UL50 TYPE 4X,6, & IEC 60529 IP66, IP67							TOLERANCES	DECIMAL	FRACTIONAL
COLOR: GLACIER GRAY							UNLESS SPECIFIED	0.000	1/16
MATERIAL	REV	BY	DATE	CHK BY	DATE	APP BY	CUSTOMER	HUBBELL WIEGMANN	
								HUBBELL WIEGMANN	
								PART NO. HW-2641683C	
								SCALE: AS SHOWN	
								ENCLOSURE	