



# N3R Screw-Cover Wall-Mount No Knockouts 4X6X4 Carbon Steel - Galvanized

By Wiegmann  
Catalog # [RSC040604GNK](#)

N3R Screw-Cover Wall-Mount No Knockouts 4X6X4 Carbon Steel - Galvanized



\*Representative Image

## Features

- Bodies and doors fabricated from 16 gauge pre-galvanized steel
- Drop shield top and smooth seamless sides and front
- A slip-on reversible cover is securely fastened with screws located along bottom edge
- No gasketing required

## General

Application	Designed for use as wiring boxes and junction boxes. Provide protection in outdoor applications against rain, sleet, and snow, or indoors against dripping water.
Construction	Spot Welded
Cover Type	Screw Cover
EU RoHS Indicator	Yes
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Embossed Mounting Holes
Type	Enclosure
UPC	786725865758

## Dimensions

Cubic Capacity	96 cu.in
Depth	4 in
Height	6 in
Weight	6.4 lb
Width	4 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	3R
UL Listed	Yes

## Logistics

Carton Quantity 5

## Product Assets

- [3D Models - RSC040604GNK](#)
- [Catalogs - Wiegmann NEMA 3R Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - RSC040604GNK-S](#)
- [Sales Drawings - HWDRSC040604GNK-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WIEG-RSC040604GNK-SPEC-EN | REV 6/2024