

# HW-151307CHQTD

By Wiegmann

Catalog ID: HW-151307CHQTD



\* Representative image

**By Wiegmann**

**Catalog ID:** HW-151307CHQTD

NEMA 4X Continuous Hinge Quarter-Turn 15X13X7  
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge with a quarter-turn style latch
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit available

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Classic
Type	Enclosure

UPC 786725879403

---

## Dimensions

---

Cubic Capacity 1365 cu.in

---

Depth 7 in

---

Height 15 in

---

Weight 11.6 lb

---

Width 13 in

---

## Certifications and Compliance

---

Certified Listed cULus

---

Nema Rating 4X

---

UL Listed Yes

---

## Logistics

---

Carton Quantity 1

---