

HW-181610CHTLW

By Wiegmann

Catalog ID: HW-181610CHTLW



* Representative image

By Wiegmann

Catalog ID: HW-181610CHTLW

NEMA 4X Continuous Hinge Link Lock With Window
18X16X10 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit is available

Product Details

General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Premier

Type	Enclosure
------	-----------

UPC	786725879892
-----	--------------

Dimensions

Cubic Capacity	2880 cu.in
----------------	------------

Depth	10 in
-------	-------

Height	18 in
--------	-------

Weight	20.3 lb
--------	---------

Width	16 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---