

HW-90705CHQTD

By Wiegmann

Catalog ID: HW-90705CHQTD



* Representative image

By Wiegmann

Catalog ID: HW-90705CHQTD

NEMA 4X Continuous Hinge Quarter-Turn 9X7X5
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge with a quarter-turn style latch
- Poured seamless gasket provides a water-tight and dust-tight seal
- Optional mounting foot kit available

Product Details

General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Classic
Type	Enclosure

UPC 786725879373

Dimensions

Cubic Capacity 315 cu.in

Depth 5 in

Height 9 in

Weight 4.3 lb

Width 7 in

Certifications and Compliance

Certified Listed cULus

Nema Rating 4X

UL Listed Yes

Logistics

Carton Quantity 1
