

HW-J2420103PT

By Wiegmann

Catalog ID: HW-J2420103PT



* Representative image

By Wiegmann

Catalog ID: HW-J2420103PT

NEMA 4X JIC Hinged 3-Point Latch 24X20X10
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge cover with 3-point latch
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725876952

Dimensions

Actual Depth	11.7 in
--------------	---------

Actual Height	27.5 in
---------------	---------

Actual Width	26.12 in
--------------	----------

Cubic Capacity	4800 cu.in
----------------	------------

Depth	10 in
-------	-------

Height	24 in
--------	-------

Weight	36 lb
--------	-------

Width	20 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---
