

HW-N4X241210CH

By Wiegmann

Catalog ID: HW-N4X241210CH



* Representative image

By Wiegmann

Catalog ID: HW-N4X241210CH

NEMA 4X Continuous Hinge Twist Latch 24X12X10
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure

UPC 786725857623

Dimensions

Cubic Capacity 2880 cu.in

Depth 10 in

Height 24 in

Weight 25 lb

Width 12 in

Certifications and Compliance

Certified Listed cULus

Nema Rating 4X

UL Listed Yes

Logistics

Carton Quantity 1
