

# HW-N4X242410CH

By Wiegmann

Catalog ID: HW-N4X242410CH



\* Representative image

**By Wiegmann**

**Catalog ID:** HW-N4X242410CH

NEMA 4X Continuous Hinge Twist Latch 24X24X10  
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure
UPC	786725857647

## Dimensions

---

Cubic Capacity	5760 cu.in
----------------	------------

---

Depth	10 in
-------	-------

---

Height	24 in
--------	-------

---

Weight	42 lb
--------	-------

---

Width	24 in
-------	-------

---

## Certifications and Compliance

---

Certified Listed	cULus
------------------	-------

---

Nema Rating	4X
-------------	----

---

UL Listed	Yes
-----------	-----

---

## Logistics

---

Carton Quantity	1
-----------------	---

---