

# HW-N4X302008CHW

By Wiegmann

Catalog ID: HW-N4X302008CHW



\* Representative image

**By Wiegmann**

**Catalog ID:** HW-N4X302008CHW

NEMA 4X Continuous Hinge Twist Latch With Window  
30X20X8 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control

Type	Enclosure
------	-----------

UPC	786725878369
-----	--------------

---

### **Dimensions**

Actual Depth	9.89 in
--------------	---------

Actual Height	32.86 in
---------------	----------

Actual Width	20.99 in
--------------	----------

Cubic Capacity	4800 cu.in
----------------	------------

Depth	8 in
-------	------

Height	30 in
--------	-------

Weight	38 lb
--------	-------

Width	20 in
-------	-------

---

### **Certifications and Compliance**

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

---

### **Logistics**

Carton Quantity	1
-----------------	---