

HW-N4X483612CHW

By Wiegmann

Catalog ID: HW-N4X483612CHW



* Representative image

By Wiegmann

Catalog ID: HW-N4X483612CHW

NEMA 4X Continuous Hinge Twist Latch With Window
48X36X12 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure

Dimensions

Actual Depth	13.93 in
--------------	----------

Actual Height	51.29 in
---------------	----------

Actual Width	36.62 in
--------------	----------

Cubic Capacity	20736 cu.in
----------------	-------------

Depth	12 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---
