

HW-N4X724824CH

By Wiegmann

Catalog ID: HW-N4X724824CH



* Representative image

By Wiegmann

Catalog ID: HW-N4X724824CH

NEMA 4X Continuous Hinge Twist Latch 72X48X24
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure

UPC 786725878802

Dimensions

Actual Depth 25.38 in

Actual Height 72.5 in

Actual Width 48.5 in

Cubic Capacity 89425 cu.in

Depth 25 in

Height 73 in

Weight 500 lb

Width 49 in

Certifications and Compliance

Certified Listed cULus

Nema Rating 4X

UL Listed Yes

Logistics

Carton Quantity 1
