

# HW-N4X727224CH

By Wiegmann

Catalog ID: HW-N4X727224CH



\* Representative image

**By Wiegmann**

**Catalog ID:** HW-N4X727224CH

NEMA 4X Continuous Hinge Twist Latch 72X72X24  
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Continuous hinge with twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	Control
Type	Enclosure

UPC	786725878888
-----	--------------

---

## Dimensions

---

Actual Depth	25.38 in
--------------	----------

---

Actual Height	72.5 in
---------------	---------

---

Actual Width	72.5 in
--------------	---------

---

Cubic Capacity	133225 cu.in
----------------	--------------

---

Depth	25 in
-------	-------

---

Height	73 in
--------	-------

---

Weight	591 lb
--------	--------

---

Width	73 in
-------	-------

---

## Certifications and Compliance

---

Certified Listed	cULus
------------------	-------

---

Nema Rating	4X
-------------	----

---

UL Listed	Yes
-----------	-----

---

## Logistics

---

Carton Quantity	1
-----------------	---

---