

# HW-RHJ100806CHSC

By Wiegmann

Catalog ID: HW-RHJ100806CHSC



\* Representative image

**By Wiegmann**

**Catalog ID:** HW-RHJ100806CHSC

NEMA 4X Hinged Extended Depth Screw Cover 10X8X6  
Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised, continuous hinge cover with two screws
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure

UPC 786725877829

---

### Dimensions

---

Cubic Capacity 480 cu.in

---

Depth 6 in

---

Height 10 in

---

Weight 5 lb

---

Width 8 in

---

### Certifications and Compliance

---

Certified Listed cULus

---

Nema Rating 4X

---

UL Listed Yes

---

### Logistics

---

Carton Quantity 1

---