

# HW-RHJ100806CHTL

By Wiegmann

Catalog ID: HW-RHJ100806CHTL



\* Representative image

By Wiegmann

Catalog ID: HW-RHJ100806CHTL

NEMA 4X Hinged Extended Depth Quick Release  
10X8X6 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC

Type	Enclosure
------	-----------

UPC	786725877911
-----	--------------

---

### Dimensions

Cubic Capacity	480 cu.in
----------------	-----------

Depth	6 in
-------	------

Height	10 in
--------	-------

Weight	5.1 lb
--------	--------

Width	8 in
-------	------

---

### Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

---

### Logistics

Carton Quantity	1
-----------------	---