

HW-RHJ121207CHTL

By Wiegmann
Catalog ID: HW-RHJ121207CHTL



* Representative image

By Wiegmann

Catalog ID: HW-RHJ121207CHTL

NEMA 4X Hinged Extended Depth Quick Release
12X12X7 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC

Type	Enclosure
------	-----------

UPC	786725877935
-----	--------------

Dimensions

Cubic Capacity	1008 cu.in
----------------	------------

Depth	7 in
-------	------

Height	12 in
--------	-------

Weight	8.8 lb
--------	--------

Width	12 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---