

HW-RHJ161407CHTLW

By Wiegmann

Catalog ID: HW-RHJ161407CHTLW



* Representative image

By Wiegmann

Catalog ID: HW-RHJ161407CHTLW

NEMA 4X Hinged Extended Depth Quick Release With Window 16X14X7 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised and windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount

Series	JIC
Type	Enclosure
UPC	786725878123

Dimensions

Cubic Capacity	1568 cu.in
Depth	7 in
Height	16 in
Weight	11.6 lb
Width	14 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---