

# HW-RHJ181610CHQRW

By Wiegmann  
Catalog ID: HW-RHJ181610CHQRW



\* Representative image

**By Wiegmann**

**Catalog ID:** HW-RHJ181610CHQRW

NEMA 4X Continuous Hinge Quick Release Padlockable Extended Cover With Window 18X16X10 Fiberglass- Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised and windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

## Product Details

### General

Color	Gray
Cover Type	Hinged Cover with Window
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC

Type	Enclosure
------	-----------

UPC	786725878215
-----	--------------

---

### **Dimensions**

Cubic Capacity	2880 cu.in
----------------	------------

Depth	10 in
-------	-------

Height	18 in
--------	-------

Weight	20 lb
--------	-------

Width	16 in
-------	-------

---

### **Certifications and Compliance**

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

---

### **Logistics**

Carton Quantity	1
-----------------	---