

HW-RHJ181610CHTLW

By Wiegmann

Catalog ID: HW-RHJ181610CHTLW



* Representative image

By Wiegmann

Catalog ID: HW-RHJ181610CHTLW

NEMA 4X Hinged Extended Depth Quick Release With Window 18X16X10 Fiberglass-Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised and windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC

Type	Enclosure
------	-----------

UPC	786725878130
-----	--------------

Dimensions

Cubic Capacity	2880 cu.in
----------------	------------

Depth	10 in
-------	-------

Height	18 in
--------	-------

Weight	19.25 lb
--------	----------

Width	16 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---