

HW-RHJ80606CHQRW

By Wiegmann

Catalog ID: HW-RHJ80606CHQRW



* Representative image

By Wiegmann

Catalog ID: HW-RHJ80606CHQRW

NEMA 4X Continuous Hinge Quick Release Padlockable Extended Cover With Window 8X6X6 Fiberglass- Opaque

Fiberglass construction is designed to protect electrical and electronic equipment in commercial or industrial environments from dust, dirt, oil, water and other corrosive materials. A wide variety of Non-Metallic enclosures are available.

- Constructed of molded fiberglass
- Raised and windowed cover with continuous hinge and quick-release padlockable latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

Product Details

General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC

Type	Enclosure
------	-----------

UPC	786725878161
-----	--------------

Dimensions

Cubic Capacity	288 cu.in
----------------	-----------

Depth	6 in
-------	------

Height	8 in
--------	------

Weight	3.7 lb
--------	--------

Width	6 in
-------	------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4X
-------------	----

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	1
-----------------	---