

RSC1212NK

By Wiegmann
Catalog ID: RSC1212NK



* Representative image

By Wiegmann

Catalog ID: RSC1212NK

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Screw-Cover Wall-Mount No Knockouts
12X12X12 Carbon Steel - Gray

Designed for use as a wiring or junction box. Provides protection in outdoor applications against rain, sleet and snow or indoors against dripping water.

- Body and cover are fabricated from carbon steel
- Slip-on reversible cover is securely fastened with screws located along the bottom edge
- No gasketing is required
- Hasp for padlocking or meter seal is provided

Product Details

General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSC

Type	Enclosure
UPC	786725880171
Dimensions	
Actual Depth	12.07 in
Actual Height	12.13 in
Actual Width	12.13 in
Cubic Capacity	1728 cu.in
Depth	12 in
Height	12 in
Weight	13 lb
Width	12 in
Certifications and Compliance	
Certified Listed	cULus
Nema Rating	1, 3R
Logistics	
Carton Quantity	2