

RSCG0404120GNK

By Wiegmann
Catalog ID: RSCG0404120GNK



* Representative image

By Wiegmann

Catalog ID: RSCG0404120GNK

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Gutter - No Knockouts 4X4X120 Carbon Steel
- Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

Product Details

General

| | |
|-------------------|-------------|
| Color | Gray |
| Cover Type | Screw Cover |
| EU RoHS Indicator | No |
| Finish Type | Galvanized |
| Material | Steel |
| Mounting Type | Wall Mount |

| | |
|--------|--------------|
| Series | RSCG |
| Type | Gutter |
| UPC | 786725884018 |

Dimensions

| | |
|---------------|-----------|
| Actual Depth | 4.06 in |
| Actual Height | 4.06 in |
| Actual Width | 120.13 in |
| Depth | 4 in |
| Height | 4 in |
| Width | 120 in |

Certifications and Compliance

| | |
|------------------|-------|
| Certified Listed | cULus |
| Nema Rating | 1, 3R |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 4 |
|-----------------|---|