

# RSCG040418NK

By Wiegmann  
Catalog ID: RSCG040418NK



\* Representative image

**By Wiegmann**

**Catalog ID:** RSCG040418NK

**Prop 65 - Cancer & Reproductive Harm Notice**

NEMA 3R Gutter - No Knockouts 4X4X18 Carbon Steel - Gray

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from carbon steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

## Product Details

### General

Color	Gray
Cover Type	Screw Cover
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSCG

Type	Gutter
------	--------

---

### **Dimensions**

---

Actual Depth	4.06 in
--------------	---------

---

Actual Height	4.06 in
---------------	---------

---

Actual Width	18.13 in
--------------	----------

---

Depth	4 in
-------	------

---

### **Certifications and Compliance**

---

Certified Listed	cULus
------------------	-------

---

Nema Rating	1, 3R
-------------	-------

---

### **Logistics**

---

Carton Quantity	4
-----------------	---

---