

# RSCG0606120NK

By Wiegmann

Catalog ID: RSCG0606120NK



\* Representative image

By Wiegmann

Catalog ID: RSCG0606120NK

**Prop 65 - Cancer & Reproductive Harm Notice**

NEMA 3R Gutter - No Knockouts 6X6X120 Carbon Steel  
- Gray

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from carbon steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

## Product Details

### General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount

Series	RSCG
Type	Gutter
UPC	786725884148

### Dimensions

Actual Depth	6.06 in
Actual Height	6.06 in
Actual Width	120.13 in
Depth	6 in
Height	6 in
Width	120 in

### Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

### Logistics

Carton Quantity	4
-----------------	---