

RSCG060696GNK

By Wiegmann

Catalog ID: RSCG060696GNK



* Representative image

By Wiegmann

Catalog ID: RSCG060696GNK

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Gutter - No Knockouts 6X6X96 Carbon Steel
- Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

Product Details

General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Galvanized
Material	Steel
Mounting Type	Wall Mount

Series	RSCG
Type	Gutter
UPC	786725884216

Dimensions

Actual Depth	6.06 in
Actual Height	6.06 in
Actual Width	96.13 in
Depth	6 in
Height	6 in
Width	96 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	4
-----------------	---