

RSCG060696NK

By Wiegmann
Catalog ID: RSCG060696NK



* Representative image

By Wiegmann

Catalog ID: RSCG060696NK

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Gutter - No Knockouts 6X6X96 Carbon Steel
- Gray

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from carbon steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

Product Details

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Wall Mount
Series	RSCG

Type	Gutter
------	--------

Dimensions

Actual Depth	6.06 in
--------------	---------

Actual Height	6.06 in
---------------	---------

Actual Width	96.13 in
--------------	----------

Depth	6 in
-------	------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	1, 3R
-------------	-------

Logistics

Carton Quantity	4
-----------------	---
