

RSCG080896G

By Wiegmann
Catalog ID: RSCG080896G



* Representative image

By Wiegmann

Catalog ID: RSCG080896G

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Gutter 8X8X96 Carbon Steel - Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge
- Knockouts are located on the bottom of the enclosure

Product Details

General

Color	Gray
Cover Type	Screw Cover
EU RoHS Indicator	No
Finish Type	Galvanized
Knockouts	Yes

Material	Steel
Mounting Type	Wall Mount
Series	RSCG
Type	Gutter
UPC	786725884278

Dimensions

Actual Depth	8.06 in
Actual Height	8.06 in
Actual Width	96.13 in
Depth	8 in
Height	8 in
Width	96 in

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

