



## RSCG101036GNK

by Wiegmann  
Catalog ID: RSCG101036GNK

N3R Gutter - No Knockouts 10X10X36 Carbon Steel - Galvanized

- Trough and cover fabricated from 16 gauge G-90 pre-galvanized steel. Drip shield top and smooth seamless sides, front and back, prevent rain, snow, and sleet from entering the enclosure. Embossed mounting holes are conveniently located on the back. A slip-on removable cover is securely fastened with screws located along the bottom edge.

### Product Details

#### General

Application	Designed to protect wiring in outdoor installations against rain, sleet and snow, or indoors against dripping water.
Construction	Spot and Tack Welded
Finish Type	Galvanized
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Embossed mounting holes
Type	Gutter
UPC	786725875269

#### Dimensions

Actual Depth	36.13 in
Actual Height	10.060 in
Actual Width	10.060 in
Cubic Capacity	3600 cu.in
Depth	36 in
Height	10 in
Weight	26 lb
Width	10 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	3R
UL Listed	Yes