

RSCG101096G

By Wiegmann

Catalog ID: RSCG101096G



* Representative image

By Wiegmann

Catalog ID: RSCG101096G

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Gutter 10X10X96 Carbon Steel - Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge
- Knockouts are located on the bottom of the enclosure

Product Details

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Knockouts	Yes
Material	Steel
Mounting Type	Wall Mount

Series	RSCG
Type	Gutter
UPC	786725884339

Dimensions

Actual Depth	10.06 in
Actual Height	10.06 in
Actual Width	96.13 in
Depth	10 in
Height	10 in
Width	96 in

Conductor Related

Cable Entry	Knock Outs
-------------	------------

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

Logistics

Carton Quantity	4
-----------------	---