

RSCG101096GNK

By Wiegmann
Catalog ID: RSCG101096GNK



* Representative image

By Wiegmann
Catalog ID: RSCG101096GNK

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 3R Gutter - No Knockouts 10X10X96 Carbon Steel - Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

Product Details

General

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Material	Steel
Mounting Type	Wall Mount
Series	RSCG

Type	Gutter
------	--------

UPC	786725884346
-----	--------------

Dimensions

Actual Depth	10.06 in
--------------	----------

Actual Height	10.06 in
---------------	----------

Actual Width	96.13 in
--------------	----------

Depth	10 in
-------	-------

Height	10 in
--------	-------

Width	96 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	1, 3R
-------------	-------

Logistics

Carton Quantity	4
-----------------	---
