

# RSCG1212120G

By Wiegmann

Catalog ID: RSCG1212120G



\* Representative image

By Wiegmann

Catalog ID: RSCG1212120G

**Prop 65 - Cancer & Reproductive Harm Notice**

NEMA 3R Gutter 12X12X120 Carbon Steel - Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge
- Knockouts are located on the bottom of the enclosure

## Product Details

### General

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Knockouts	Yes
Material	Steel
Mounting Type	Wall Mount

Series	RSCG
Type	Gutter
UPC	786725884360

### Dimensions

Actual Depth	12.06 in
Actual Height	12.06 in
Actual Width	120.13 in
Depth	12 in
Height	12 in
Width	120 in

### Conductor Related

Cable Entry	Knock Outs
-------------	------------

### Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 3R

### Logistics

Carton Quantity	4
-----------------	---