

# RSCG121296GNK

By Wiegmann

Catalog ID: RSCG121296GNK



\* Representative image

**By Wiegmann**

**Catalog ID:** RSCG121296GNK

## **Prop 65 - Cancer & Reproductive Harm Notice**

NEMA 3R Gutter - No Knockouts 12X12X96 Carbon Steel  
- Galvanized

Designed to protect wiring in outdoor installations against rain, sleet and snow or indoors against dripping water.

- Trough and cover are fabricated from galvanized steel
- Drip shield prevents rain, snow and sleet from entering the enclosure
- Mounting holes are located on the back of the enclosure
- Slip-on removable cover is securely fastened with screws located along the bottom edge

## Product Details

### **General**

Color	Gray
Cover Type	Screw Cover
Finish Type	Galvanized
Material	Steel
Mounting Type	Wall Mount
Series	RSCG

Type	Gutter
------	--------

UPC	78672588351
-----	-------------

---

### **Dimensions**

Actual Depth	12.06 in
--------------	----------

Actual Height	12.06 in
---------------	----------

Actual Width	96.13 in
--------------	----------

Depth	12 in
-------	-------

Height	12 in
--------	-------

Width	96 in
-------	-------

---

### **Certifications and Compliance**

Certified Listed	cULus
------------------	-------

Nema Rating	1, 3R
-------------	-------

---

### **Logistics**

Carton Quantity	1
-----------------	---