

T2272CHSS

By Wiegmann

Catalog ID: T2272CHSS



* Representative image

By Wiegmann

Catalog ID: T2272CHSS

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 4X Hinge Cover Wire Trough 2.5 X 2.5 X 72 304 Stainless Steel

The T_CHSS Series wiring trough is designed to protect internal components and wiring from dust, dirt, oil and water. This trough can be used indoors or outdoors as well as in corrosive environments.

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

Product Details

General

Cover Type	Hinged Cover
------------	--------------

EU RoHS Indicator	No
-------------------	----

Finish Type	Grained Stainless Steel
-------------	-------------------------

Latches Type	External Clamps
--------------	-----------------

Material	304 Stainless Steel
----------	---------------------

Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888566

Dimensions

Actual Depth	72.31 in
Actual Height	4 in
Actual Width	4 in
Depth	72 in
Height	2.5 in
Weight	20.5 lb
Width	2.5 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

Logistics

Carton Quantity	1
-----------------	---