

T4418CHSS

By Wiegmann

Catalog ID: T4418CHSS



* Representative image

By Wiegmann

Catalog ID: T4418CHSS

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 4X Hinge Cover Wire Trough 4 X 4 X 18 in. 304 Stainless Steel

The T_CHSS Series wiring trough is designed to protect internal components and wiring from dust, dirt, oil and water. This trough can be used indoors or outdoors as well as in corrosive environments.

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

Product Details

General

Cover Type

Hinged Cover

Finish Type

Grained Stainless Steel

Latches Type

External Clamps

Material

304 Stainless Steel

Mounting Type

Wall Mount

Number of Doors (Fixed)	1
-------------------------	---

Series	T_CHSS
--------	--------

Dimensions

Actual Depth	18.31 in
--------------	----------

Actual Height	5.5 in
---------------	--------

Actual Width	5.5 in
--------------	--------

Depth	18 in
-------	-------

Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	1, 12, 4 & 4X
-------------	---------------

Logistics

Carton Quantity	1
-----------------	---
