

# WA121204GSCSS

By Wiegmann

Catalog ID: WA121204GSCSS



\* Representative image

By Wiegmann

Catalog ID: WA121204GSCSS

## Prop 65 - Cancer & Reproductive Harm Notice

NEMA 4X Gasketed Screw Cover 12X12X4 304 Stainless Steel

Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.

- Bodies and covers are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

## Product Details

### General

Application	Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained

Material	304 Stainless Steel
----------	---------------------

Mounting Type	Wall
---------------	------

Number of Doors (Fixed)	1
-------------------------	---

### Dimensions

Actual Height	12.125 in
---------------	-----------

Actual Width	12.125 in
--------------	-----------

Cubic Capacity	576 cu.in
----------------	-----------

Depth	4 in
-------	------

### Certifications and Compliance

Certified Listed	cULus
------------------	-------

Nema Rating	4, 4X, 12, 13
-------------	---------------

### Logistics

Carton Quantity	1
-----------------	---