

WADW131602BCSS

By Wiegmann

Catalog ID: WADW131602BCSS



* Representative image

By Wiegmann

Catalog ID: WADW131602BCSS

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 4X Deep Hinged Blank Cover 12.8X15.9X2.8 304 Stainless Steel

The Wiegmann Universal Deep Hinged Door Kit is styled after Wiegmann's N412 Ultimate Series enclosures. Kits are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

- Quarter-turn style latching for easy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment

Product Details

General

Accessory Type	Window/Door Kit
----------------	-----------------

EU RoHS Indicator	No
-------------------	----

Finish Type	Stainless Steel
-------------	-----------------

Latches Type	Quarter Turn Latch
--------------	--------------------

Material	304 Stainless Steel
----------	---------------------

Type	Accessory
------	-----------

UPC 786725885497

Dimensions

Actual Depth 2.75 in

Actual Height 12.75 in

Actual Width 15.88 in

Depth 2 in

Height 13 in

Width 16 in

Certifications and Compliance

Certified Listed UL Recognized 508A

Nema Rating 4X

Logistics

Carton Quantity 1
