

WADW292002BCSS

By Wiegmann

Catalog ID: WADW292002BCSS



* Representative image

By Wiegmann

Catalog ID: WADW292002BCSS

Prop 65 - Cancer & Reproductive Harm Notice

NEMA 4X Deep Hinged Blank Cover 29.8X20.3X2.8 304 Stainless Steel

The Wiegmann Universal Deep Hinged Door Kit is styled after Wiegmann's N412 Ultimate Series enclosures. Kits are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

- Quarter-turn style latching for wasy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment

Product Details

General

Accessory Type Window/Door Kit

Color Stainless Steel

Finish Type Stainless Steel

Latches Type Quarter Turn Latch

Material 304 Stainless Steel

Type Accessory

UPC 786725885558

Dimensions

Actual Depth 2.75 in

Actual Height 28.75 in

Actual Width 20.25 in

Depth 2 in

Height 29 in

Width 20 in

Certifications and Compliance

Certified Listed UL Recognized 508A

Nema Rating 4X

Logistics

Carton Quantity 1
