

Data sheet

Commercial Art.No.: 25.330.3306.0

PCB pin header 8113 S / 3 G OB THR

PCB pin header, connection method depends on used socket part , 3 poles, with solder pin (2.6mm, tin plated), pitch: 5 mm, type of packing: carton, color: black, This product can be soldered by reflow and wave soldering,



certificates / approvals



Technical data

general

modular spacing	5 mm
soldering process	THR
packaging	carton
number of poles	3
number of levels	1
marking	no
fastening	none
mating direction towards (circuit) board	90°

technical data

rated current	12 A
overvoltage category I	1000 V
overvoltage category II	400 V
overvoltage category III	250 V
rated impulse voltage	4 kV

technical data UL/CSA

voltage UL	300 V
current field wiring	15 A
current factory wiring	15 A
voltage CSA	300 V
current CSA	15 A

other

type of insulation material	thermoplastic
-----------------------------	---------------

color	black
height	12 mm
length	17 mm
depth	8.4 mm
material contact base	CuZn
material contact surface	Sn

classification

ECLASS 11	
ECLASS 8.1	27440402
ETIM 9.0	EC002637
ETIM 8.0	EC002637
ETIM 7.0	EC002637
ETIM 6.0	EC002637
ETIM 5.0	EC002637
ETIM 4.0	EC002637

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant