


## Data sheet

Commercial Art.No.: 57.904.4855.0

compensating terminal 9785U/5 KOHM-SPT/V0

Compensating terminal block with screw connection for mounting on TS 35 and TS 32, nominal cross section 4 mm<sup>2</sup>, width 12 mm, color g ray



Commercial Art.No.	57.904.4855.0
EAN	4015573605701
Order Unit	50

## Technical data

### general

nominal cross section	2.5 mm <sup>2</sup>
color	grey
number of levels	2
number of clamp positions per level	2
width/grid dimension	12 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
mounting method	DIN rail (top hat rail)/G-rail
terminal blocks for electrical installations	no
type of component	potenziometer
Anzahl der Klemmstellen je Etage	2
Montageart	DIN rail (top hat rail)/G-rail
Brennbarkeitsklasse des Isolierstoffs	V0
Reihenklennen für Installationsverteiler	no

### technical data

pollution degree	3
closing plate required	no
type of insulation material	thermoplastic
length	49 mm

### connection data

connection type 1	screw connection
connection type 2	screw connection
minimum cross section solid	0.5 mm <sup>2</sup>
maximum cross section solid	2.5 mm <sup>2</sup>
minimum cross section fine stranded	0.5 mm <sup>2</sup>
maximum cross section fine stranded	2.5 mm <sup>2</sup>
wire strip length	9 mm
torque conductor mounting	0.5 Nm

### classification

ECLASS 11	
ECLASS 8.1	27141127

ETIM 9.0	EC000903
ETIM 8.0	EC000903
ETIM 7.0	EC000903
ETIM 6.0	EC000903
ETIM 5.0	EC000903
ETIM 4.0	EC000903
ETIM 3.0	EC000903

**product compliance**

ROHS conformity status	compliant/exempted
ROHS exceptions	III-6(c)
REACH-SVHC conformity status	Duty-To-Declare
REACH-SVHC substances	Lead
REACH-SVHC CAS numbers	7439-92-1

**Accessories**

<b>Commercial Art.No.:</b>	<b>Article-type description:</b>	<b>Description:</b>
--------------------------------	----------------------------------	---------------------