

Data sheet

Commercial Art.No.: 92.232.9007.1

cable assembly GST18i3K1BD 15 90SW

gesis® CLASSIC mains connection cable, female - power plug, number of poles 3, rated voltage 250 V, rated current 16 A, cable type H05VV-F, fire class Eca, total length 9 m, nominal cross section conductor 1.5 mm², color of coding/ contact carrier black



certificates / approvals



Technical data

general

rated current	16 A
rated voltage	250 V
rated impulse voltage	4 kV
pollution degree	2
mechanical coding	code 1
continuity resistor	103.6 mOhm
lockable	self-locking (unlocking by tool)
color of coding/ contact carrier	black
Pole codification	L, N, PE
color of housing inclusive strain relief	black

model

nominal cross section conductor	1.5 mm ²
degree of protection (IP)	IP20
cable type	H05VV-F
cable color	black
cable diameter max.	8.3 mm
version of cable	female - power plug
type of cord set	mains connection cable
version cable end 1	GST18i3 female
version cable end 2	CEE 7/7

material

surface finish	tin-plated
halogen free	no

continuous temperature of cable	70 °C
insulation components continuous temperature	100 °C
fire load	0 kWh/St
fire class	Eca

dimensions

total length	9 m
--------------	-----

classification

ECLASS 11	
ECLASS 8.1	27440604
ETIM 9.0	EC002587
ETIM 8.0	EC002587
ETIM 7.0	EC002587
ETIM 6.0	EC002587
ETIM 5.0	EC002587
ETIM 4.0	EC002587

product compliance

ROHS conformity status	compliant/exempted
ROHS exceptions	III-6(c)
REACH-SVHC conformity status	Duty-To-Declare
REACH-SVHC substances	Lead
REACH-SVHC CAS numbers	7439-92-1