

Data sheet

Commercial Art.No.: Z1.298.2053.0

fuse disconnect lever THSI 6,3X32 GL 500

Fuse disconnect lever for diconnect terminal blocks selos / fasis / taris



certificates / approvals



Technical data

general

color	grey
width/grid dimension	8 mm
insulating housing	PA666
flammability class of insulation material acc. with UL94	V0
mounting method	direct mounting
fuse insert	G-fuse 6.3x32 mm
Montageart	direct mounting
Brennbarkeitsklasse des Isolierstoffs	V0

technical data

rated voltage	500 V
closing plate required	no
type of insulation material	thermoplastic
length	57.3 mm

additional data

remark to rated voltage	note fuse insert
remark to rated current	note fuse insert
defect indicator	glow lamp
voltage type for defect indication	AC/DC
minimum operating voltage of defective display	380 V
maximum operating voltage of defective display	500 V

classification

ECLASS 11	
-----------	--

ECLASS 8.1	27141116
ETIM 9.0	EC000899
ETIM 8.0	EC000899
ETIM 7.0	EC000899
ETIM 6.0	EC000899
ETIM 5.0	EC000899
ETIM 4.0	EC000899
ETIM 3.0	EC000899

product compliance

ROHS conformity status	compliant
REACH-SVHC conformity status	compliant