

Datasheet

Item No. 70.331.1635.1

Bottom BAS GUT GC 16 M25 50 A1

revos BASIC 500V size 16 closed-bottom base with threaded collar M25, left double locking lever



Item No.	70.331.1635.1
EAN	4015573599567
order unit	1 Piece(s)

Approvals



Technical data

**General**

ArticlePrice	udp_no_price
Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

**Model**

DIN-size	16
Model	Surface mounting (base)
Locking mechanism	Double locking levers
Cable entry	Sideways
Type of cable	Thread
With cable screw gland	No
Thread size M	25
Hinged lid	No
EMC-version	No

Drawings