

Datasheet

Item No. 70.333.0635.1

Bottom BAS GUT GO 6 M20 50 A1

revos BASIC 500V size 6 closed-bottom base with threaded collar M20, bottom single locking lever



Item No.	70.333.0635.1
EAN	4015573599598
order unit	1 Piece(s)

Approvals



Technical data

General

ArticlePrice	udp_no_price
Nominal voltage	500
Housing material	Aluminium
Colour	Grey
Surface	With powder coating
Degree of protection (IP)	Other
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

DIN-size	6
Model	Surface mounting (base)
Locking mechanism	Single locking lever
Cable entry	Below
Type of cable	Thread
With cable screw gland	No
Thread size M	20
Hinged lid	No
EMC-version	No