

Datasheet

Item No. 70.352.1035.0

Hood BAS GOT GC 10 M20 50 A0

revos BASIC 500V size 10 hood with cable gland M20, top cable entry, double locking lever



| | |
|------------|---------------|
| Item No. | 70.352.1035.0 |
| EAN | 4015573616905 |
| order unit | 1 Piece(s) |

Approvals



Technical data

General

| | |
|--|---------------------|
| ArticlePrice | udp_no_price |
| Nominal voltage | 500 |
| Housing material | Aluminium |
| Colour | Grey |
| Surface | With powder coating |
| Degree of protection (IP) | IP54 |
| UV resistant | Yes |
| Inflammability class of insulation material acc. with UL94 | Other |
| Operating temperature range min. | -40 °C |
| Operating temperature range max. | 120 °C |

Model

| | |
|------------------------|-----------------------|
| DIN-size | 10 |
| Model | male |
| Locking mechanism | Double locking levers |
| Cable entry | Above |
| Type of cable | Gland nut |
| With cable screw gland | Yes |
| Thread size M | 20 |
| Hinged lid | No |
| EMC-version | No |

Drawings