

## Datasheet

Item No. 70.355.1635.1

Hood BAS GOT GD 16 M25 50 A1

revos BASIC 500V size 16 hood with threaded collar M25, lateral cable entry, with double locking levers



|            |               |
|------------|---------------|
| Item No.   | 70.355.1635.1 |
| EAN        | 4015573606135 |
| order unit | 1 Piece(s)    |

### Approvals



### Technical data

#### General

|  |                     |
|--|---------------------|
| ArticlePrice   | udp_no_price        |
| Nominal voltage  | 500                 |
| Housing material   | Aluminium           |
| Colour   | Grey                |
| Surface  | With powder coating |
| Degree of protection (IP)                                  | Other               |
| UV resistant   | Yes                 |
| Inflammability class of insulation material acc. with UL94 | Other               |
| Operating temperature range min.                           | -40 °C              |
| Operating temperature range max.                           | 120 °C              |

#### Model

|                        |                       |
|------------------------|-----------------------|
| DIN-size               | 16                    |
| Model                  | male                  |
| Locking mechanism      | Double locking levers |
| Cable entry            | Sideways              |
| Type of cable          | Thread                |
| With cable screw gland | No                    |
| Thread size M          | 25                    |
| Hinged lid             | No                    |
| EMC-version            | No                    |

Drawings